

LUXURA X5 38

12 MINUTES

ProSun
INTERNATIONAL LLC



EQUIPMENT SPECS

Canopy Lamps	22 x 160W
Bench Lamps	16 x 180W
Facial Lamps	3 x 400W
Session Time	12 Minutes
Dimensions	90.2"L x 53.5"W x 61.4"H
Recommended Room Size	9 ft. x 9 ft.
AC Requirements	BTU 9000 A/C
Shipping Weight	975 lbs.
Shipping Dimensions	91" x 46" x 65"

EQUIPMENT FEATURES

- T-Max Integrated
- QuickStart Function
- Adjustable Body & Facial Cooling
- Ambient FlowLight
- XL Light
- Contoured Acrylic
- Touch Screen Display
- Stand-by Inside Lighting
- Optional: Electronic Ballast
- Optional: AC
- Optional: Sound Around Plus
- Optional: SD Sound Cards
(Wellness, Studio, SmartVoice)
- Optional: BlueTooth
- Optional: Qsens
- Optional: Xsens 1
- Optional: Xsens 3

ELECTRICAL RATING

3 Phase	
Electrical Rating	230V 3~28A 60 Hz 3 Pole (3 Hots 1 Ground)
Power Requirements	40 Amp
Buckbooster	2 * 1.0 Kva
Single Phase	
Electrical Rating	230V~45A 60 Hz 2 Pole (2 Hots 1 Ground)
Power Requirements	60 Amp
Buckbooster	1 * 1.5 Kva

PROSUN.COM - 727.825.0400

Note: *Equipment comes standard in three phase configuration. Buck boosters must be installed by licensed electrician in your state/county

**ProSun reserves the right to change design and specifications without notice.*

800.874.2776 • Sales@prosun.com • 2442 23rd St. N. St. Petersburg, FL 33713 • 510(K): K181455

Contraindication: This product is contraindicated for use on persons under the age of 18 years. "Contraindication: This product must not be used if skin lesions or open wounds are present." "Warning: This product should not be used on individuals who have had skin cancer or have a family history of skin cancer." "Warning: Persons repeatedly exposed to UV radiation should be regularly evaluated for skin cancer.