

# LUXURA X7

12 MINUTES / 10 MINUTES

**ProSun**  
INTERNATIONAL LLC



## EQUIPMENT SPECS

Canopy Lamps	12 Min: 24 x 160W 10 Min: 24 x 200W
Bench Lamps	12 Min: 18 x 180W 10 Min: 18 x 200W
Facial Lamps	4 x 400W
Session Time	12 Minutes or 10 Minutes
Dimensions	90.5"L x 53.5"W x 61.4"H
Recommended Room Size	9 ft. x 9 ft.
AC Requirements	BTU 9000 A/C
Shipping Weight	1,100 lbs.
Shipping Dimensions	91" x 46" x 55"

## EQUIPMENT FEATURES

**T-Max Integrated**  
**QuickStart Function**  
**Adjustable Body & Facial Cooling**  
**Ambient FlowLight**  
**XL Light**  
**Contoured Acrylic**  
**Touch Screen Display**  
**Stand-by Inside Lighting**  
*Optional:* Lamp Upgrade to 10 min bed  
*Optional:* Electronic Ballast  
*Optional:* AC  
*Optional:* Sound Around Plus  
*Optional:* SD Sound Cards  
(Wellness, Studio, SmartVoice)  
*Optional:* Bluetooth  
*Optional:* Qsens  
*Optional:* Xsens 1 or 3

## ELECTRICAL RATING

### 3 Phase

Electrical Rating	230V 3~32A 60 Hz 3 Pole ( 3 Hots 1 Ground)
Power Requirements	40 Amp
Buckbooster	2 * 1.0 Kva

### Single Phase

Electrical Rating	230V 50A 60 Hz 2 Pole ( 2 Hots 1 Ground)
Power Requirements	60 Amp
Buckbooster	1 * 1.5 Kva

**PROSUN.COM - 727.825.0400**

**Note: \*Equipment comes standard in three phase configuration. Buck boosters must be installed by licensed electrician in your state/county**

*\*ProSun reserves the right to change design and specifications without notice.*

**800.874.2776 • Sales@prosun.com • 2442 23rd St. N. St. Petersburg, FL 33713 • 510(K): K181455**

Contraindication: This product is contraindicated for use on persons under the age of 18 years. "Contraindication: This product must not be used if skin lesions or open wounds are present." "Warning: This product should not be used on individuals who have had skin cancer or have a family history of skin cancer." "Warning: Persons repeatedly exposed to UV radiation should be regularly evaluated for skin cancer.